

# 1-1/2” Tubing Pump Specifications

## Traveling Valves

- Available in 4 cup, 8 cup, and cuptex (4 cup/23 flange ring) configurations
- Top open cage with 5/8” API sucker rod pin connection
- Uses standard 1-1/2” cups, flange rings, and ball/seat

## Standing Valves

- Cup seating with 2 HR seating cups
- Uses standard 1-1/2” HR seating cups and ball/seat

## Barrels

- 1.750” OD x 1.500” ID available in 4’, 5’, and 6’ lengths
- 1.750-16 pin threaded ends
- Honed to proper size and finish in house with our Sunnen Tube Hone

## Connecting Collars

- 1.900 10RD NUE x 1.750-16 upper connecting collars
- 1.900 10RD NUE x 1.750-16 lower connecting/seating collars

